

# Tflex UT20000 Recommended Directions for Use

#### Shelf Life:

Shelf life for Tflex UT20000 is 1 year from date of shipment at the storage conditions specified below.

## **Storage Conditions:**


Recommended storage conditions are 0-35°C at relative humidity of 50% maximum. Please store in original product packaging until ready for use.


#### **Product Form:**


Sheets, Rolls

# **Application Instructions:**

- 1. Remove the diamond liner by separating it from the pad at one corner. Peel back the liner in consistent motion as close to an 180<sup>o</sup> angle as possible.
- 2. Fold the die cutting gap filler and push the gap filler from the corner to make it separate from the clear liner.
- 3. Peel off the gap filler from the clear liner and place it onto desired substrate.
- 4. Cover the exposed gap filler or continue the assembly process to avoid contamination of the surface from dust and debris.







### **Revision Log**

Rev.	Summary of Change	Requested By	Approval Date
Α	Initial Release	Mandy Feng	10/21/2016
В	change product name from Tflex UT200 to Tflex UT20000	Mandy Feng	1/3/2017